

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® T:1.67 With 30mm and 50mm EFL Achromats, 30mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock #46-004 3-4 DAYS



1



€227,00

ADD TO CART

Qty 1-5

€227,00

Qty 6+

€181,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):  
22.0

Center Air Spacing (mm):  
2.12

Substrate: [N-BAF10](#) / [N-SF10](#) / [N-BAF10](#) / [N-SF10](#)

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Surface Quality:</b><br>40-20                                      |
| <b>Working f#:</b><br>f/2.16                                          |
| <b>Coating:</b><br>MgF <sub>2</sub> (400-700nm)                       |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @400 - 700nm |
| <b>Effective Focal Length EFL A (mm):</b><br>30.00                    |
| <b>Effective Focal Length EFL B (mm):</b><br>50.00                    |
| <b>Housing Diameter (mm):</b><br>30 +0.0/-0.10                        |
| <b>Housing Length (mm):</b><br>34 ±0.2                                |
| <b>Lens Edge Spacing at Mount (mm):</b><br>8                          |
| <b>Magnification:</b><br>1:1.67                                       |
| <b>Object Distance (mm):</b><br>19.19                                 |
| <b>Image Distance (mm):</b><br>39.68                                  |
| <b>Construction:</b><br>Achromat Pair in Anodized Aluminum Housing    |
| <b>Type:</b><br>Relay Lens                                            |
| <b>Wavelength Range (nm):</b><br>400 - 700                            |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |