

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Zero Series

Stock #57-600 3-4 DAYS



1



€330,00

ADD TO CART

Qty 1-4

€330,00

Qty 5+

€291,30

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
75.0

Outer Diameter (mm):
117.0

Construction: Anodized Aluminum Alloy, Stainless Steel Leaves
Full Angular Range of Lever (°): 97.00
Lever Length (mm): 53.00
Lever Position (mm): 4.8
Lever Size (mm): 15.00 x 5.00
Number of Leaves: Two sets of 9
Operating Temperature (°C): <400
Pin Thread & Pitch: N/A
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant