

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-861 3-4 DAYS



1



€704,00

ADD TO CART

Qty 1+

€704,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:  
White

Model Number:  
HLV3-22SW-2-1220

Dimensions (mm):  
22 x 42.6 x 49 (W x D x H), Tip diameter 12 mm

Weight (g):  
47

Power Consumption (W):  
2.5

|                                                 |
|-------------------------------------------------|
| <b>Active Area (mm):</b><br>6                   |
| <b>Color Temperature (K):</b><br>5600           |
| <b>Type of Illumination:</b><br>LED Illuminator |
| <b>Manufacturer:</b><br>CCS                     |
| <b>Geometry:</b><br>Spot Light                  |
| <b>Maximum Input Current:</b><br>700mA          |
| <b>Illumination Mode:</b><br>Constant           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Reach 224:</b><br><a href="#">Contains SVHC(s)</a>      |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |