

1.25", Red 625nm, High Intensity Pattern Projecting Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity Pattern Projecting Spot Lights

Stock **#18-637** 3-4 DAYS

- 1 + **€966,00**

ADD TO CART

Qty 1+

€966,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
Red

Diameter (inches):
1.25

Model Number:
SL256-625IC

Operating Temperature (°C):
0 - 50

Wavelength (nm): 625.00
Weight (g): 413
Diameter of Compatible Reticle (mm): 20.8
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m): 2
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant
Environmental Rating: IP50
Minimum Input Current: 0.592

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)