

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® T:2.5 with 40mm and 100mm EFL Achromats, 30mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock #46-010 3-4 DAYS



1



€227,00

ADD TO CART

Qty 1-5

€227,00

Qty 6+

€181,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
22.0

Center Air Spacing (mm):
4.11

Substrate: ☐
[S-BAH11](#) / [N-SF10](#) / [N-BK7](#) / [N-SF5](#)

Surface Quality: 40-20
Working f#: f/4.51
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Effective Focal Length EFL A (mm): 40.00
Effective Focal Length EFL B (mm): 100.00
Housing Diameter (mm): 30 +0.0/-0.10
Housing Length (mm): 34 ±0.2
Lens Edge Spacing at Mount (mm): 8
Magnification: 1:2.50
Object Distance (mm): 29.31
Image Distance (mm): 90.13
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View