

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

12.5 X 17.5mm, 70R/30T, Plate Beamsplitter



Stock #45-317 3-4 DAYS

- 1 + €47,00

ADD TO CART

Qty 1-9

€47,00

Qty 10+

€33,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:

Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR 1/λ MgF₂ @ 550nm

Construction:

Plate

Dimensional Tolerance (mm):

±0.38

Dimensions (mm): 12.5 x 17.5
Edges: Cut
Reflection/Transmission Ratio (R/T): 70/30
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant