

TECHSPEC® 12.5mm Dia 40R/60T, VIS Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock **#68-381** 3-4 DAYS

⊖ 1 ⊕ **€103,00**

ADD TO CART

Qty 1-5

€103,00

Qty 6+

€82,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: 40/60 ±5% @ 550nm, ±10% @ 400 -

700nm Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 400 - 700nm
Construction: Plate
Diameter (mm): 12.50
Edges: Cut with 0.25mm maximum edge chip
Note: Beamsplitter-coated side is marked with a black dot
Parallelism (arcmin): ≤ 3
Reflection/Transmission Ratio (R/T): 40/60
Substrate: ☐ N-BK7
Surface Flatness (P-V): 1 λ per inch
Surface Quality: 60-40
Thickness (mm): 3.00 $\pm$ 0.25
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant