


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #36-652 3-4 DAYS



1



€418,00

ADD TO CART

Qty 1-9

€418,00

Qty 10+

€367,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
±20

Clear Aperture CA (mm):
11.25

Diameter (mm):
12.50

Extinction Ratio:

100,000:1
Substrate: Soda Lime Float Glass
Operating Temperature (°C): -20 to +120
Surface Quality: 40-20
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >84
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Nanoparticle
Clear Aperture (%): 90
Transmitted Wavefront, P-V: < λ/4
Beam Deviation (arcmin): <1
Polarization Axis Mark (%): ±2
Wavelength Range (nm): 600 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 197: Compliant
Certificate of Conformance: View