

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5mm Dia. Uncoated, NTO Fused Silica Window



TECHSPEC® Uncoated Laser Window Substrates

Stock #48-022 3-4 DAYS



1



€120,00

ADD TO CART

Qty 1-5

€120,00

Qty 6+

€108,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Clear Aperture CA (mm):

11.25

Coating:

Uncoated

Diameter (mm): 12.50 +0.00/-0.10
Substrate: Fused Silica Excimer Grade (Corning 7980 KrF)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Laser Line Window
Bevel: Protective as needed
Clear Aperture (%) : 90
Transmitted Wavefront, P-V: λ/10
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤5
Wavelength Range (nm): 200 - 2200
Fused Silica Grade: 7980 KrF 0A
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View