

TECHSPEC®

12.5mm Dia x 75mm FL VIS-NIR Coated, Illumination Grade PCX Cylinder Lens



Stock #69-771 3-4 DAYS

-

1

+

€82,00

ADD TO CART

Qty 1-5
€82,00
Qty 6+
€65,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
N-BK7

f/#: 6
Numerical Aperture NA: 0.08
Coating: VIS-NIR (400-1000nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): 73.68
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.49
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 38.76
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant