

[See all 205 Products in Family](#)

TECHSPEC[®]

125mm Diameter Protected Gold Coated, $\lambda/10$ Mirror



Stock **#70-926** 1 In Stock

-

1

+

€1.135^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€1.135,00 each
Qty 6-25	€910,00 each
Qty 26-49	€855,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

125.00

Diameter (mm):

12.50 ±0.20

Thickness (mm):

	Back Surface:
Commercial Polish	
	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Edges:
Ground	

	Parallelism (arcsec):
30	

Optical Properties

	Wavelength Range (µm):
0.7 - 10	

	Coating Type:
Metal	

	Coating:
Protected Gold (700-10000nm)	

	Surface Flatness (P-V):
λ/10	

	Wavelength Range (nm):
700 - 10000	

	Substrate: □
Fused Silica (Corning 7980)	

	Coating Specification:
R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	

	Surface Quality:
20-10	

	Damage Threshold, Reference: □
0.8 J/cm ² @ 1064nm, 10ns	

Regulatory Compliance

	RoHS 2015:
Compliant	

	Certificate of Conformance:
View	

	Reach 247:
Compliant	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

TECHSPEC® λ/10 First Surface Mirrors are ideal for demanding beam steering and reflection applications in the visible and IR spectra. With a precision fused silica substrate, the mirrors feature a low coefficient of thermal expansion while being highly durable and resistant to abrasion. These precision mirrors are available in a variety of sizes and coating options, including enhanced aluminum, protected gold, and protected silver. These coatings allow for improved handling of the component, increased durability of the metal coating, and protection from oxidation with little impact to the performance on the metal coating. TECHSPEC® λ/10 First Surface Mirrors can be utilized in various optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

Note: Surface flatness is measured before coating.