

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #63-224 ☐ In Stock



1



€50,00

ADD TO CART

Qty 1-10

€50,00

Qty 11+

€40,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 ±0.25

Grit: ☐
220

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant