



12.5mm H x 25mm L x -12.5mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#68-052** 3-4 DAYS

- 1 + **€62,00**

ADD TO CART

Qty 1-5

€62,00

Qty 6+

€49,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-12.50

Substrate:
[N-SF11](#)

Coating:

Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -13.9
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 4.51
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -9.81
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View