



12.5mm H x 25mm L x -150mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #68-060 3-4 DAYS

- 1 + **€62,00**

ADD TO CART

Qty 1-5
€62,00

Qty 6+
€49,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-150.00

Substrate: N-BK7

Coating:

Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -151.65
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 2.73
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -77.52
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View