

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC®

12.5mm H x 25mm L x -20mm FL MgF₂ Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #68-071 3-4 DAYS



1



€71,50

ADD TO CART

Qty 1-5

€71,50

Qty 6+

€57,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-20.00

Substrate:
[N-SF11](#)

Coating:

MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -21.4
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 3.67
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -15.69
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant