



12.5mm H x 25mm L x -50mm FL VIS 0° Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #69-799 3-4 DAYS

- 1 + **€82,00**

ADD TO CART

Qty 1-5
€82,00

Qty 6+
€65,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-50.00

Substrate: N-BK7

Coating:

MS 0° (425-675nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -51.65
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 3.19
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -25.84
Surface Quality: 60-40
Damage Threshold, Reference:  5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant