

TECHSPEC® 125mm, Side Drive, Standard Top, English Micrometer Stage



125mm Micrometer Drive Stage

Stock **#66-454** 3-4 DAYS

⊖ 1 ⊕ **€580,00**

ADD TO CART

Qty 1-2

€580,00

Qty 3+

€505,90

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
English Micrometer

Drive Orientation: Side Drive
Type: English
Stage Size (mm): 125 x 125
Travel (inches): 1
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 20
Mounting Threads: (21) 1/4-20, (8) 2-56, (4) 6-32
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
