

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT



Rack & Pinion Track

Stock #56-795 □ In Stock



1



€141,00

ADD TO CART

Qty 1+

€141,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:  
Linear (X)

Type of Drive:  
Rack and Pinion

Type:  
Metric

Travel (mm):  
125

Construction:

|                                                   |
|---------------------------------------------------|
| Black Anodized Aluminum                           |
| <b>Graduation (mm):</b><br>1                      |
| <b>Load Capacity, Normal (kg):</b><br>5           |
| <b>Load Capacity, Vertical (kg):</b><br>2         |
| <b>Mounting Threads:</b><br>N/A                   |
| <b>Note:</b><br>Track                             |
| <b>S.H.C.S. C'bore:</b><br>(4) 6.5mm Thru         |
| <b>Travel Per Knob Rotation (mm):</b><br>18       |
| <b>Straight Line Accuracy (mm):</b><br>0.1 - 0.25 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Reach 224:</b><br><a href="#">Contains SVHC(s)</a>      |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

