

TECHSPEC[®] S-Mount, 12.5mm x 17.6mm Plate Mount



Plate S-Mount Holder (#11-142)

Stock **#11-142** 2 In Stock

-

1

+

€278⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€278,00 each
Qty 5-9	€260,00 each
Qty 10-25	€247,40 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Optic Mount (Fixed)

Function:

Rectangular

Type of Optics:

Includes one S-Mount Aperture Cap ([# 11-137](#))

Note:

12.5 x 17.6

30.0 x 30.0 x 28.5

Dimensions (mm):

30.0

Extension Length (mm):

1.0

Min. Thickness of Compatible Optics (mm):

3.0

Max. Thickness of Compatible Optics (mm):

S-Mount

Thread Type:

1/4-20

Compatible Post:

Compliant

RoHS 2015:

View

Certificate of Conformance:

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

1" -32 C-Mount
Thread 4 places

50.00

27.45
4 sides

19.00
4 sides

38.00 Sq.

Units: mm