

12.7 x 12.7mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#69-244** 3-4 DAYS

⊖ 1 ⊕ **€15,00**

ADD TO CART

Qty 1-5
€15,00

Qty 6+
€12,00

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm): 12.7 x 12.7 ±0.76
Coating Specification: R_{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 1.60
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 12.70
Width (mm): 12.70

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant