

TECHSPEC® 12.7 x 12.7mm EFL 90° Protected Gold 100Å Off-Axis Parabolic Mirror



Stock **#35-484** 3-4 DAYS

[Other Coating Options](#)



1



€285,00

ADD TO CART

Qty 1-5

€285,00

Qty 6+

€256,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
12.70 +0.00/-0.38

Effective Focal Length EFL (mm):

12.70
Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 12.70
Coating : Protected Gold (700-10000nm)
Coating Type : Metal
Coating Specification : R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°) : 90
Parent Focal Length PFL (mm) : 6.35
Surface Figure, RMS : λ/4
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 700 - 10000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #34-425
Substrate : Aluminum 6061-T6
Y Offset (mm) : 12.7
Reflected Wavefront, RMS : λ/2

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant