

TECHSPEC® 127 x 127mm, Enhanced Aluminum, 4-6λ Mirror



Stock **#18-934** 3-4 DAYS

- 1 + **€69,50**

ADD TO CART

Qty 1-5
€69,50
Qty 6+
€55,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

127.00 x 127.00 +0.00/-0.25
Coating Specification: R _{avg} ≥95% @ 450 - 650nm @ 45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 114.30 x 114.30
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 (nominal)
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 127.00
Width (mm): 127.00
Damage Threshold, By Design: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant