

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #49-680 3-4 DAYS



1



€4.030,00

ADD TO CART

Qty 1+

€4.030,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcsec):
5.00

Clear Aperture CA (mm):
127.0

Coating:
Protected Gold (700-2000nm)

Diameter (mm):
166.70

Exiting Wavefront Accuracy:
3.0λ

Substrate: 

Surface Quality:
80-50

Mounting Threads:
(7) ¼-20, (6) M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
700 - 2000

Regulatory Compliance

RoHS 2015:
Compliant

REACH 201:
Compliant

Certificate of Conformance:
[View](#)