

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Pellicle Beamsplitters

Stock #19-310 3-4 DAYS



1



€212,00

ADD TO CART

Qty 1-10

€212,00

Qty 11+

€180,20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
12.7

Coating:
Dielectric

Coating Specification:

50/50 @ 632.8nm
Construction: Pellicle
Design Wavelength DWL (nm): 632.8
Diameter (mm): 19.05
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 3.18
Reflection/Transmission Ratio (R/T): 50/50 ±5%
Substrate: ☐ Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Mounting Threads: 2-56
Thickness (µm): 2 +0.3/-0.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View