


12.7mm Dia 50R/50T, VIS-NIR Polka-Dot Beamsplitters



VIS-NIR Polka-Dot Beamsplitters

Stock #15-983 3-4 DAYS

⊖ 1 ⊕ **€118,00**

ADD TO CART

Qty 1-10

€118,00

Qty 11+

€100,30

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):

90
Coating: Square Aluminum (AlMgF ₂) Apertures
Construction: Polka-Dot
Diameter (mm): 12.70 +0.0/-0.5
Minimum Aperture (mm): 2.00
Operating Temperature (°C): 150 Maximum
Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5 @ 45°
Substrate: B270
Surface Quality: 80-50
Thickness (mm): 1.65 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 2000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View