


TECHSPEC® 12.7mm Dia. λ /10 ZERODUR® Optical Flat



Stock #43-327-000 ☐ In Stock

1 **€93,00**

ADD TO CART

Qty 1-10

€93,00

Qty 11+

€84,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
 λ /10

Abbe Number (v_d):
56.2

Coating:

Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Diameter (mm): 12.70 +0.0/-0.50
Thickness (mm): 3.20 ±0.8
Diameter (inches): 0.50 +0.00/-0.02
Thickness (inches): 0.13 ±0.03
Clear Aperture CA (mm): 11.40
Color: Yellow Tint
Construction: Single Surface
Density (g/cm³): 2.53
Index of Refraction n_d: 1.542
Knoop Hardness (kg/mm²): 620
Parallelism (arcmin): ≤3
Poisson's Ratio: 0.24
Substrate: ZERODUR®
Surface Quality: 60-40
Type: Interferometry Window
Young's Modulus (GPa): 90.3
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View