

12.7mm, ISP Optics Germanium Equilateral Prism | GE-EP-12

See More by [ISP Optics](#)



Stock #19-711 3-4 DAYS

- 1 + **€1.395,00**

ADD TO CART

Qty 1-5
€1.395,00

Qty 6+
€1.116,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating: Uncoated
Substrate: ☐ Germanium (Ge)
Surface Quality:

60-40
Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85
Length of Hypotenuse (mm): 12.70
Length of Legs (mm): 12.70
Wavelength Range (nm): 2000 - 14000
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 2λ
Model Number: ZC-EP-12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View