

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region:

European Union

SUBMIT



Stock #18-715

3-4 DAYS

- 1 +

 €145,00

ADD TO CART

Qty 1-10

€145,00

Qty 11+

€123,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):
90

Coating: Square Aluminum (AlMgF ₂) Apertures
Construction: Polka-Dot
Dimensional Tolerance (mm): +0.0/-0.5
Dimensions (mm): 12.7 x 12.7
Minimum Aperture (mm): 2.00
Operating Temperature (°C): 150 Maximum
Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 80/20
Reflection/Transmission Tolerance (%): ±5 @45°
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 80-50
Thickness (mm): 1.65 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 250 - 2000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View