

[See all 4 Products in Family](#)

## 12mm Dia. x 48mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-074 CLEARANCE **15 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €20<sup>50</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€20,50 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Plano-Convex Lens **Type:**

### Physical & Mechanical Properties

12.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

**Center Thickness CT (mm):**

2.00

Edge Thickness ET (mm):

1.26

Clear Aperture CA (mm):

≥10.2

### Optical Properties

Effective Focal Length EFL (mm):

48.00

Back Focal Length BFL (mm):

46.69

Coating:

Uncoated

Substrate: □

[N-BK7](#)

Focal Length Tolerance (%):

±1

Radius  $R_1$  (mm):

24.81

f#:

4.00

Numerical Aperture NA:

0.13

### Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF<sub>2</sub> Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

## Technical Information

