

TECHSPEC® 12mm Dia. x -12mm FL, Uncoated, Double-Concave Lens



Stock **#32-988** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€30,50**

ADD TO CART

Qty 1-9
€30,50
Qty 10+
€27,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-12.00
Substrate: N-SF11
f#: 1.00
Numerical Aperture NA: 0.50
Coating: Uncoated
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -12.81
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Edge Thickness ET (mm): 4.71
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -19.47
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View