

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

12" X 12" , 0.010" FL, Lenticular Array



Stock #43-029 3-4 DAYS



1



€128,00

ADD TO CART

Qty 1-10

€128,00

Qty 11+

€112,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):

0.25

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Lens Array
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Center Thickness CT (mm): 1.50
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 12 x 12
Dimensions (mm): 304.8 x 304.8
Effective Focal Length EFL (inches): 0.01
Effective Size (inches): 12 x 12
Index of Refraction n_d: 1.49
Number of Lenses: 142 per 25.4mm
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Thickness Tolerance (mm): ±0.6

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View