

TECHSPEC® 1.3 OD 12.5mm Diameter, Reflective ND Filter



Stock **#46-134** CLEARANCE 3-4 DAYS

- 1 + **€34,00**

ADD TO CART

Qty 1-5
€34,00
Qty 6+
€27,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0

Optical Density OD (Average):
1.3

Substrate: Float Glass
Coating: Surface 1: Inconel
Reflection (%) : 50.00
Surface Quality : 80-50
Thickness (mm) : 1.60 Nominal
Transmission (%) : 5.00
Type : Neutral Density Filter
Blocking Wavelength Range (nm) : 400 - 700
Dimensional Tolerance (mm) : ±0.5
Clear Aperture (%) : 80
Neutrality : ±5% of Optical Density
Note : Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V) : 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant