

1350nm CWL, 12nm FWHM, 25mm Mounted Diameter



Stock #65-789 3-4 DAYS

⊖ 1 ⊕ **€201,00**

ADD TO CART

Qty 1-9

€201,00

Qty 10+

€180,70

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm):

21.0

Center Wavelength CWL (nm):

1,350.00 ±2.5

Center Wavelength CWL Tolerance (nm):

±2.5

Full Width-Half Max FWHM (nm):

12.00 ±2.5

Full Width-Half Max FWHM Tolerance (nm):

±2.5

Minimum Transmission (%):

>70

Operating Temperature (°C):

-50 to +75

Coating:

Traditional Coated

Surface Quality:

80-50

Thickness Tolerance (mm):

±0.1

Type:

Bandpass Filter

Typical Applications:

Clinical Chemistry

Blocking Wavelength Range (nm):

200 - 1500

Construction:

Mounted in Black Anodized Ring

Mount Thickness (mm):

7.5 ±0.1

Regulatory Compliance

RoHS 2015:[Compliant](#)**Certificate of Conformance:**[View](#)**Reach 240:**[Compliant](#)