

[See all 11 Products in Family](#)

## 13mm Travel, 0.01mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock #33-727 **1 In Stock**

€91.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€91,00 each
Qty 10-24	€81,90 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Metric **Type:**  
Mitutoyo **Manufacturer:**

### Physical & Mechanical Properties

13 **Travel (mm):**

0.01	Graduation (mm):
9.5	Stem Diameter (mm):
Plain/Spherical	Stem/Spindle:
9.5	Stem Length (mm):
5	Spindle Diameter (mm):
15.5	Min. Spindle Length (mm):
13	Max. Diameter (mm):
62	Overall Length (mm):

## Hardware & Interface Connectivity

Metric Micrometer	Type of Drive:
-------------------	----------------

## Regulatory Compliance

<a href="#">Exempt</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Contains SVHC(s)</a>	REACH 241:

## Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.