

# 13mm Travel, Fine Screw, Thru-Hole Ball Bearing Stage



32mm/1.25" Center drive stage and its X-Y-Z configuration

Stock **#56-356** 3-4 DAYS



1



€391,00

ADD TO CART

Qty 1+

€391,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Ball Bearing

Type of Drive:  
Fine Screw (64 Pitch)

Drive Orientation:  
Center Drive

Type:

| Metric                                                      |
|-------------------------------------------------------------|
| <b>Stage Size (mm):</b><br>31.8 x 32.5                      |
| <b>Travel (mm):</b><br>12.7                                 |
| <b>Construction:</b><br>Aluminium Stage                     |
| <b>Graduation (mm):</b><br>No                               |
| <b>Height (mm):</b><br>12.7                                 |
| <b>Load Capacity, Normal (kg):</b><br>3                     |
| <b>Load Capacity, T<sub>a</sub> (kg):</b><br>4.5            |
| <b>Note:</b><br>Thru-Hole                                   |
| <b>Straight Line Accuracy (µm):</b><br>2 per 25mm of travel |
| <b>Weight (kg):</b><br>0.078                                |
| <b>Thrust Capacity, T<sub>a</sub> (kg):</b><br>4.5          |
| <b>Thrust Capacity, T<sub>b</sub> (kg):</b><br>1.4          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |