

140mm Length, Adjustable Laser Holder



#56-332, #56-333

Stock **#56-332** **5 In Stock**

⊖ 1 ⊕ €375.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€375,00 each
Qty 5-25	€331,50 each
Qty 26-49	€305,30 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Adjustable - Tilt **Type:**

Cylindrical Tube **Type of Optics:**

Physical & Mechanical Properties

Length (mm):

140.00

740

Weight (g):

Construction:

Black Anodized Aluminum

Twin Ring Mount Adjustment Screw Pitch (mm):

0.5

Tilt Angle (°):

±4

Threading & Mounting

Size of Compatible Optics (mm):

20.0 - 55.0

Compatible Post:

M6 x 1.0

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Contains SVHC\(s\)](#)

Product Details

- Twin Ring Mount Design
- Fixed and Adjustable Versions
- Ideal for He-Ne Lasers
- [Posts](#) and [Post Holders](#) Required for Mounting

Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Mounting hole is M6 x 1.0

Technical Information

