

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #24-717 CLEARANCE 3-4 DAYS



1



€216,95

ADD TO CART

Qty 1+

€216,95

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
14.00 ±0.01

Substrate: ☐  
Calcium Fluoride (CaF<sub>2</sub>), IR Grade

Coating:  
Uncoated

Type:  
Half-Ball Lens

|                                                       |
|-------------------------------------------------------|
| <b>Wavelength Range (nm):</b><br>300 - 8000           |
| <b>Center Thickness CT (mm):</b><br>7.00 ±0.05        |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.434 |
| <b>Model Number:</b><br>CF-HS-14                      |
| <b>Radius R (mm):</b><br>7.00                         |
| <b>Surface Quality:</b><br>60-40                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |