

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

152.4mm Clear Aperture 40R/40T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock #39-499 3-4 DAYS



1



€990,00

ADD TO CART

Qty 1-10

€990,00

Qty 11+

€841,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
152.4

Coating:
Metal/Dielectric

Coating Specification:

40/40 @ 400 - 700nm
Construction: Pellicle
Diameter (mm): 165.10
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 9.53
Reflection/Transmission Ratio (R/T): 40/40 $\pm$ 5%
Substrate: ☐ Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Wavelength Range (nm): 400 - 700
Mounting Threads: 6-32
Thickness (μm): 2 +0.3/-0.0

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View