

152.4mm Clear Aperture 50R/50T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-501** 3-4 DAYS



1



€990,00

ADD TO CART

Qty 1-10

€990,00

Qty 11+

€841,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
152.4

Coating:
Dielectric

Coating Specification:

50/50 @ 632.8nm
Construction: Pellicle
Design Wavelength DWL (nm): 632.8
Diameter (mm): 165.10
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 9.53
Reflection/Transmission Ratio (R/T): 50/50 ±5%
Substrate: ☐ Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Mounting Threads: 6-32
Thickness (µm): 2 +0.3/-0.0

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View