

[See all 5 Products in Family](#)

15.8mm Dia x 71mm FL, Grade 1, Plano-Convex Lens



Stock #74-074 CLEARANCE **2 In Stock**

⊖ 1 ⊕ €10²⁵

ADD TO CART

Volume Pricing	
Qty 1+	€10,25 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

15.80 **Diameter (mm):**

Optical Properties

71.00 **Effective Focal Length EFL (mm):**

Anti-Reflection Coating Coating:

4.49 f#:

0.11 Numerical Aperture NA:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

