

15.8mm Dia x 71mm FL, Grade 1, Plano-Convex Lens



Stock **#74-074** CLEARANCE **2 In Stock**

-

1

+

€10^{,25}

ADD TO CART

Volume Pricing	
Qty 1+	€10,25 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

15.80

Optical Properties

Effective Focal Length EFL (mm):

71.00

Anti-Reflection Coating	Coating:
4.49	f/#:
0.11	Numerical Aperture NA:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Ideal for Experimenting and Prototyping Applications
 - Quantities Extremely Limited, Buy While Supplies Last
 - For Even More Deals, Check out [Mega Clearance: Optics](#)
- Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

