


TECHSPEC® 15mm 50R/50T NIR Cube Beamsplitter



Stock #14-641 3-4 DAYS

⊖ 1 ⊕ **€207,00**

ADD TO CART

Qty 1-5
€207,00

Qty 6+
€165,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Coating:
λ/4 MgF₂ @ 900nm on Faces
Multilayer Dielectric on Hypotenuse

Construction: Cube
Dimensions (mm): 15.0 x 15.0 x 15.0 ±0.10
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Quality: 40-20
Type: Standard Beamsplitter
Wavelength Range (nm): 700 - 1100
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View