

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC®
15mm Dia., 0.66 Numerical Aperture, 900-1700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock #16-994-INK [CONTACT US](#)

[Other Coating Options](#)



1



€325,00

ADD TO CART

Qty 1-5

€325,00

Qty 6+

€260,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
15.00 ±0.025

Effective Focal Length EFL (mm):

11.25 @ 587.6nm
Numerical Aperture NA: 0.66
Back Focal Length BFL (mm): 5.71
Substrate: 
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: SWR+ (900-1700nm)
Coating Specification: R _{avg} <0.5% @ 900 - 1700nm @ ±30° AOI R _{abs} <1.5% @ 900 - 1700nm @ ±30° AOI
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 13.50
Edge Thickness ET (mm): 6.67
Center Thickness CT (mm): 10.00 ±0.10
f#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 900 - 1700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View