

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 15mm Dia. X 20mm FL, Uncoated, Double-Convex Lens



Stock #63-543 ☐ In Stock
[Other Coating Options](#)

1 €30,00

ADD TO CART

Qty 1-9
€30,00
Qty 10+
€27,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Back Focal Length BFL (mm):

18.99
Effective Focal Length EFL (mm): 20.00
Coating: Uncoated
Substrate: 
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.63
Radius R ₁ =R ₂ (mm): 30.60
Clear Aperture CA (mm): 14.00
f/#: 1.33
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.38
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant