

15mm Square IR Cut-Off Filter



Stock #53-709 ☐ In Stock

-

1

+

€42,50

ADD TO CART

Qty 1-24
€42,50
Qty 25+
€35,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
15.0 x 15.0

Cut-Off Wavelength (nm):
710.00

Substrate: ☐
[BOROFLOAT®](#)

Length (mm):

15.00
Operating Temperature (°C): <250
Coating: Traditional Coated
Index of Refraction n_d: 1.472
Surface Quality: 80-50
Thickness (mm): 1.10
Thickness Tolerance (mm): ±0.25
Type: IR Cut-Off Filter
Width (mm): 15.00
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥90
Edges: Seamed Edges
Coating Specification: Surface 1: T=50% @ 710±30nm, T _{avg} >85% @ 480 - 680nm, T _{avg} <10% @ 740 - 1200nm Surface 2: <i>N</i> /4 MgF ₂
Wavelength Range (nm): 480 - 1200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant