

[See all 22 Products in Family](#)

1.67mm FL CS-Mount, Manual Iris, Wide Angle Lens



1.67mm FL CS-Mount, Manual Iris, Wide Angle Lens, #64-105

Stock **#64-105** **1 In Stock**

⊖ 1 ⊕ €558.⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €558,00 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
Low Distortion Wide Angle Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

Length (mm):

| | |
|-------|-------------------------------|
| 56.00 | |
| 36.0 | Maximum Diameter (mm): |
| 36 | Outer Diameter (mm): |
| 80.00 | Weight (g): |

Optical Properties

| | |
|----------------|---|
| 110° | Horizontal Field of View, 1/3" Sensor: |
| 7.20 | Maximum Image Circle (mm): |
| 1.67 | Focal Length FL (mm): |
| 100 - ∞ | Working Distance (mm): |
| f/1.8 - Closed | Aperture (f#): |
| <1 | Distortion (%): |
| <1 | Maximum Distortion (%): |
| VS | Lens Wavelength Range: |

Sensor

| | |
|--------|-------------------------------|
| 1/2.5" | Maximum Sensor Format: |
| 4.50 | Pixel Size (µm): |

Threading & Mounting

| | |
|----------|-----------------------|
| N/A | Filter Thread: |
| CS-Mount | Mount: |

Regulatory Compliance

| | |
|----------------------------------|------------------------------------|
| Exempt | RoHS 2015: |
| Contains SVHC(s) | Reach 223: |
| View | Certificate of Conformance: |

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.