

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

16mm Dia. x 10.8mm FL, Uncoated Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#34-459** ☒ In Stock

☐ [Other Coating Options](#)



1



€31,50

ADD TO CART

Qty 1-10

€31,50

Qty 11+

€27,90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
16.00 +/-0.3

Effective Focal Length EFL (mm):
10.80 @ 587.6nm

Numerical Aperture NA:
0.74

Back Focal Length BFL (mm): 5.90
Substrate: N-F2
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 12.80
Edge Thickness ET (mm): 2.6
Center Thickness CT (mm): 8.00 ±0.20
f/#: 0.68
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 16.0
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant