

[See all 5 Products in Family](#)

## 16mm Fixed Focal Length Lens



#86-207

Stock **#86-207** [CONTACT US](#)

- 1 + €2.043<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€2.043,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Product Family:**  
4/3" Format Fixed Focal Length Lenses

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**

79.50	
45.0	<b>Maximum Diameter (mm):</b>
45	<b>Outer Diameter (mm):</b>
250.00	<b>Weight (g):</b>

## Optical Properties

60.6	<b>Horizontal Field of View @ Max Sensor Format:</b>
135.00	<b>Field of View @ Min Working Distance (mm):</b>
21.60	<b>Maximum Image Circle (mm):</b>
16.00	<b>Focal Length FL (mm):</b>
100 - ∞	<b>Working Distance (mm):</b>
f/2 - f/22	<b>Aperture (f#):</b>
<0.1	<b>Distortion (%):</b>
0.02	<b>Maximum Distortion (%):</b>
VS	<b>Lens Wavelength Range:</b>

## Sensor

4/3"	<b>Maximum Sensor Format:</b>
5.00	<b>Pixel Size (µm):</b>

## Threading & Mounting

M40.5 x 0.50	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>

## Product Details

- Up to 1", C-Mount Lens
- Less than 1.0% TVDistortion
- 12mm to 50mm Focal Length

Available in multiple focal lengths, 4/3" Format Fixed Focal Length Lenses incorporate a floating focus with aspheric lenses to maximize resolution across their entire working distance. Ideal for many machine vision applications, these fixed focal length lenses feature a broadband anti-reflection (AR) coating for maximum transmission. 4/3" Format Fixed Focal Length Lenses are available with focal lengths ranging from 12 - 50mm.