

16mm FL SWIR Series Fixed Focal Length Lens



Stock #83-817 3-4 DAYS

- 1 + **€2.105,00**

ADD TO CART

Qty 1+
€2.105,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
235

Iris Option:
Variable

Length (mm):
52.90

Filter Thread:
M34.5 x 0.50

Maximum Diameter (mm):
42.0

Weight (g): 150
Horizontal Field of View, 1" Sensor: 44.3°
Maximum Image Circle (mm): 16.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 16.00
Maximum Sensor Format: 1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Distortion (%): <-1.0
Lens Wavelength Range: SWIR

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)