

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

1.8 - 3.0mm FL CS-Mount, Auto Iris, Wide Angle Lens



1.28mm FL C-Mount, Manual Iris, Wide Angle Lens, #62-050



Stock #85-163 CONTACT US

- 1 +

€465,00

ADD TO CART

Qty 1+

€465,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
50.00

Maximum Diameter (mm):
39.0

Weight (g):

70.00
Horizontal Field of View, 1/3" Sensor: 105 - 77°
Type: Varifocal Lens
Focal Length FL (mm): 1.80 - 3.00
Maximum Sensor Format: 1/2.5"
Working Distance (mm): 500 - ∞
Mount: CS-Mount
Style: Auto Iris
Aperture (f/#): f/1.8 - Closed
Distortion (%): <1
Lens Wavelength Range: VS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View